

FumeVent Lab Smart

Laboratory Exhaust System

Features

- Factory expanded pipe and fitting ends
- Fusion welded pipe seams
- Fully welded fittings
- 4" through 24" diameters
- Constructed from:
 - 20 GA Stainless Steel
 - 304L/316L Stainless Steel

Benefits

- Air and watertight seams
- Meets SMACNA's RT-6 Standard
- Field labour savings

Lab Smart Design

- Cut to length on site
- Directional exhaust flow
- Self supporting connections

Applications

- Anaesthetic gas scavenging systems
- Hot lab exhaust
- Bio-safety cabinets
- Cart wash exhaust



FLEXMASTER CANADA 

Email: sales@flexmaster.com
Website: www.flexmaster.com

Calgary, AB
Delta, BC
Etobicoke, ON
Pointe Claire, PQ
Richmond Hill, ON

tel: 403-277-3115 fax: 403-276-1309
tel: 604-940-6401 fax: 604-940-6402
tel: 416-679-0045 fax: 416-679-0051
tel: 514-697-3701 fax: 514-697-3767
tel: 905-731-9411 fax: 905-731-7086

The information provided within is for informational purposes only. We have made every effort to ensure the accuracy of the provided information and assume no responsibility for any loss or damage due to errors or omissions or to the use or misuse of any information supplied. It is impossible to test all products under all conditions to which they might be subjected in the field. It is therefore the buyer and/or end users' responsibility to test all products under the conditions that duplicate the service conditions prior to installation. All improvements, all specifications are subject to change without prior notice. It is the buyer and/or end users' responsibility to review our complete **Terms and Conditions of Sale** located on our web sites at: www.novaflex.com | www.z-flex.com | www.flexmaster.com.